



INTELLIGENT SOLUTIONS

TO REDUCE SPACE MISSION COSTS



MAGNETIC TORQUER ACTUATORS FOR GNC

Magnetic Torquers interact with Earth's magnetic field and create control torque, which can be adjusted to the required value. Combined with one or more re-action wheels, they provide all the control needed to maintain the spacecraft's attitude. Unlike thrusters torquers do not need valuable consumables, are low power components and highly reliable.

Design Features

- Internal coil fixation to eliminate mechanical and thermal stress
- Nickel-alloy cores with special treatment
- Aluminium brackets (custom designs available)
- Aluminium-alloy or composite housing tube
- Heavy grade coil wire insulation
- Simultaneous winding of redundant coils
- ESCC non-magnetic connectors or flying leads
- Titanium bolts and housing parts
- Air coil systems using aluminium or CFRP are available

Our production process satisfies the highest standards for performance and workmanship with excellent quality control.

PHILOSOPHY

"IN THE PAST 15, YEARS ZARM TECHNIK AG HAS GAINED A LARGE FLIGHT HERITAGE ...

up to 1.000 Am² and can therefore table solution. Nevertheless, if this should not be the case, ZARM Technik is offering as a free-of-charge service the customization of individual units. provide a customized magnetic torquer

ZARM Technik Magnetic Torquers supported more than 100 international satellite missions. Not a single magnetic torquer out of over 500 units has ever failed. For more than 15 years we produce and improve intelligent technical solutions to reduce space mission costs. Our experience led to an outstanding flight heritage and satisfied clients all over the world.



MAGNETOMETER
SENSORS FOR GNC

Magnetometers have been part of the attitude determination and control system (ADCS) of satellite missions since the beginning of space flight. They measure the external magnetic field as input for the attitude control system.

Two different sensor concepts for magnetic field measurement

onboard the satellites are
available: Fluxgate magnetometer
with noise below
one nT which
is built with high
reliable components
and a well-prized
Anisotropic Magnetoresistive (AMR) based

magnetometer with lower

resolution but compact size and low mass.

Performance

- Low power consumption
- Low mass and size
- ▶ Good linearity and accuracy
- ▶ Radiation tolerant > 50 kRAD
- Adaptation to specific mission requirements is available

Design Features

- Aluminium-alloy housing
- Encapsulant protects the sensor and electronics inside the housing
- Space-grade materials and qualified EEE parts
- ESCC D-subminiature or MDM-type non-magnetic connectors

SERVICES

FOR TESTING SPACE HARDWARE

TVAC:

Environmental testing is mandatory for space hardware to qualify for vacuum and thermal conditions faced during the hardware's life span in space. ZARM Technik's facilities offer services required for manufacturing like Bake-out. Our qualification standards are according to ESA and NASA procedures.

▶ Vibrational Testing:

The Shaker allows the simulation of launch loads on the hardware. Ground testing and evaluating all aspects of vibrational and structural dynamic characteristics is a vital step in assuring a robust and successful design. This includes random vibrations, sine sweeps and shock conditions.

▶ Hyper-g Testing:

ZARM Technik operates the largest centrifuge in Europe offering high acceleration levels up to 30g — complementary to the drop towers zero-g environment. The testing facility enables certifications of aerospace structures and prototypes under conditions of crash survival.















HOUSING TUBE

STANDARD ANODIZED MATT BLACK FINISH SHOWS OPTIMIZED THERMO-OPTICAL PROPERTIES – ADDITIONALLY AVAILABLE ARE CFRP AND PEEK.





ACCOMMODATES CONNECTOR
AND GROUNDING – AVAILABLE
VARIETIES INCLUDE DIFFERENT
OUTLET DIRECTIONS AND
FLYING LEADS.

KAPTON

CORE INSULATION.

SIGNATURE

OUR UPPER
HOUSING PLATE
CARRIES THE
TORQUERS
UNIQUE
ENGRAVING.



BRACKETS

MOUNTING INTERFACE TO SPACE-CRAFT – NUMBER AND POSITION CAN BE VARIED ACCORDING TO CUSTOMER REQUEST – THERMAL COUPLING WITH SPACECRAFT.

ELASTOMER

PROVIDES COIL PROTECTION AND INTERNAL FLOATING COIL FIXATION TO ELIMINATE MECHANICAL AND THERMAL STRESS.

MAGNETIC CORE

OUTSTANDING MATERIAL TREATMENT ASSURES BEST MAGNETIZABILITY.

THE IMPACT ON DESIGN IS VALUED HIGH WITH OUR CUSTOMERS.

NEAR ZERO HYSTERESIS – EXCELLENT LINEARITY – HIGH MAX DIPOLE MOMENT.

COIL

AT THE HEART OF OUR CUSTOM MADE TORQUERS IS THE INDIVIDUAL COMBINED DESIGN OF COIL AND CORE AND THE ADAPTION TO SPECIFIC MISSION REQUIREMENTS.

MAGNETIC TORQUER CUSTOM-MADE FROM 0.1AM² UP TO 1000AM²

Although torquers appear to relatively simple devices, they request thoughtful design and careful assemble. The torquer's key feature component — its core material — has be treated to ensure optimal magne properties. Each unit is total encapsulated and, except for the co

components.

designs have been realised satisfying the customer's specific technical requirements by adapting power consumption, dipole range, size, and mass.





ZARM Technik AG is one of the leading suppliers for attitude control equipment. It was founded in 1997 as a spin-off company and commercial branch of the university institute ZARM.

Today ZARM Technik AG produces and delivers space technology products for small low-cost satellites as well as for large scale constellations.

ZARM Technik AG

Holger W. Oelze, CEO

Am Fallturm | 28359 Bremen | Germany

Phone +49 421 218-57770 | Fax +49 421 218-9857770

holger.w.oelze@zarm-technik.de www.zarm-technik.de

ZARM, Center of Applied Space Technology and Microgravity, is the largest university space research center in Europe, its most outstanding facility is the Drop Tower Bremen, which provides up to 9.3 seconds of microgravity.